

TT 570 Standard Micromanometer



Pressure	Velocity
± 0 to 7.50 KPa ± 0 to 30.0 inH ₂ O	0.70 to 90.0 m/sec 138 to 17730 ft/min

Pressure:



Features:

- Back Light
- Area Setting
- Auto Zeroing
- Single Battery
- Average Velocity
- Pitot Tube Factor
- Average Pressure
- Store up to 2500 Readings
- Air Density Correction Factor



The TT 570 Standard Micromanometer with its unique differential capacitance transducers and programmable auto zero facility stores up to three Pitot Tube factors, up to four duct settings and a maximum of 2500 readings.

Readings can be downloaded to PC in basic format with optional download software.

Velocity with Ellipsoidal Pitot Static Tube:



Weighing 555 g, measuring 45 x 92 x 185 mm and powered by a single battery; the TT 570 Standard Micromanometer is ideal for the modern engineer.

Standard Accessories:

- 2 x 6 mm Tubing Adaptors (2)
- 3 m x 2 mm Bore Flexible Tubing (2)
- Calibration Certificate
- Instruction Manual
- Neck Sling
- Soft Lined Case

Optional Extras:

- dpm Ane™
- Download Software
- Pitot Static Tubes
- Rubber Holster
- Test Set Case

Pressure							Velocity				
Models:							Range / Resolution:				
570	570 SV	570 MV	570 AV	570 BV	570 CV	570 DV	Pressure:				
●	●				●	●	KPa	± 0 to 99.9 Pa	± 100 to 999 Pa	± 1.00 to 7.50 KPa	
●		●			●	●	mmH ₂ O	± 0 to 0.999	± 1.00 to 9.99	± 10.0 to 99.9	± 100 to 750
●			●		●	●	inH ₂ O	± 0 to 9.999	± 1.00 to 9.99	± 10.0 to 30.0	
●				●	●	●	mbar	± 0 to 0.999	± 1.00 to 9.99	± 10.0 to 75.0	
							Velocity : Ellipsoidal		dpm-i	dpm Ane™	
	●	●		●	●		m/sec	2.00 to 90.0	0.70 to 30.0	0.70 to 25.0	
			●			●	ft/min	394 to 17730	138 to 5905	138 to 4921	

Accuracy:

Pressure at 20°C, Velocity with Ellipsoidal Pitot Static Tube at 16°C, 1000 mbar:

Readings < 100 counts ± 2 counts. Readings > 100 counts ± 1% of reading ± 1 count.

Velocity with dpm-i Pitot Tube at 16°C, 1000 mbar:

± 3% of reading or ± 0.05 m/sec (10 ft/min) ± 1 count. Whichever is greater.

Velocity with dpm Ane™ at 16°C, 1000 mbar:

Readings up to 8 m/sec (1575 ft/min) ± 1% of reading ± 0.03 m/sec.

Readings from 8 to 25 m/sec (1575 to 4921 ft/min) ± 1 m/sec (197 ft/min)

General Specifications:

Recommended Operational Limits:	0° to 50°C (32° to 123°F)
Span Stability versus Temperature:	0.1% of range in use per °C (per 2°F)
Zero Drift:	Negligible due to auto zero system When auto zero set a 60 second intervals (2 minute warm up)
Zero System Accuracy:	± 0.05 Pascal typical
Orientation Effect:	(any 45° change) 0.1 Pascal typical
Output Socket:	RS 232 (baud rate 9600)
Data Logging:	Up to 2500 any units
Software:	Download data to PC in very basic form
Power Source:	Dry Cell (MN1604, PP3) or Rechargeable
System Air Leak:	0.1 ml/minute at 5 KPa (typical)
Safe Line / Differential Pressure:	15KPa
Storage Temperature Limits:	-5° to +50°C
Weight:	555 g with battery
Dimensions:	45 x 92 x 185 mm



In the interest of continuous product development and improvement DP Measurement reserve the right to amend specifications and discontinue models, features and colours of the TT Series and dpm Ane™ at any time without prior notice.

Manufactured in UK

Distributed by:



DP Measurement

Unit 11, Top Angel, Buckingham Industrial Park
Buckingham, England. MK18 1TH
Tel / Fax +44 (0)1280 817122
www.ttseries.com email dpm@ttseries.com



Associated Instrument Repairs

Unit 11, Top Angel, Buckingham Industrial Park
Buckingham, England. MK18 1TH
Tel / Fax +44 (0)1280 823823
www.a-i-r.co.uk email air@ttseries.com